

PAG Softlight Diffuser Kit

Model 9983

1. The PAG Softlight Diffuser & Filter Set comprises:

Filter Holders (x2)

The Filter Holders are designed to slide onto the parallel barndoors of the Paglight (Model 9954 - not included in this kit). The same assembly will also fit onto the barndoors of the smaller Paglight M and Paglight C6.

The Filter Holders have two hooks onto which are hung the Softlight Diffuser or any of the filters supplied in this kit.

The Filter Holder assembly can be easily removed and reapplied when necessary. For the correct assembly see the illustration opposite.

PAG Softlight Diffusers (x2)

The Softlight Diffuser creates a soft even light ideal for use with any of the Paglight plug-in lampholder options.

Full CT Blue Filters (x2)

The full blue filter converts the colour temperature of the light output from tungsten (3200°K) to daylight (5700°K).

Half CT Blue Filters (x2)

The half blue filter converts the colour temperature of the light output from tungsten (3200°K) to daylight (4300°K), and provides a warmer effect than the full blue.

Half CT Orange Filters (x2)

The half orange filter converts the colour temperature of the light output from daylight to tungsten (3800°K).

2. Replacement or additional filter packs:

The following packs are also available:

9984 Filter Holders (x2).

9979 PAG Softlight Diffusers (x6).

9980 Full CT Blue Filters (x6).

9981 Half CT Orange Filters (x6).

9982 Half CT Blue Filters (x6).

